



bar

AGD4200-USB

Digital Pressure Transmitter



FEATURES

- Pressure ranges from vacuum to 5,000 bar
- Sample rate software selection up to 1,000 Hz
- Silicon-on-Sapphire pressure sensor technology
- Free USB® downloadable software with auto update
- Measure & record up to 16 pressure inputs together
- Create customised test certificates
- Automatic temperature compensation
- Support for easy integration with applications created by C#, VB, Labview and Excel VBA (api dll library)
- 2m lead & carry case included



The award winning AGD4200-USB digital pressure transmitter is facilitated by the USB® Windows interface software, giving the user full control of the monitoring, recording, and analysis of pressure data.

The digitally self scaling software provides accurate, high resolution measurement at a precision greater than 1 in 10,000 and is compatible with Windows 8 | 8.1 | 10 | 11.

SPECIFICATIONS (DYNAMIC AGD4200-USB DIGITAL PRESSURE TRANSMITTER)

The Dynamic AGD4200-USB digital pressure transmitter offers reliable and accurate pressure measurement from vacuum to 5000 bar. It is specifically designed to measure, analyse, and record pressure directly to your PC without the need of costly I/O interface boards. The easy „plug and play“ nature of the unit allows the user to easily download the free USB® software and view live pressure data in as little as 10 minutes.

The unique Silicon-on-Sapphire sensor technology provides outstanding performance and gives excellent stability over a wide temperature range. Excellent measurement accuracy provides high resolution with a precision greater than 1 in 10,000. Ten pressure ranges have been carefully selected to enable the user to cover any pressure that the application requires, from vacuum up to 5,000 bar, via the use of the USB® digitally self-scaling software.

Each unit is supplied with 2m USB lead (rated to IP68), and a convenient carry case.

Typical applications include:


- Test and Measurement
- Laboratory or process measurement
- Leak testing and continuous monitoring



DIMENSIONS (in mm)

ELECTRICAL CONNECTIONS

- USB Mini B Socket




USB-SOFTWARE (DYNAMIC AGD4200-USB DIGITAL PRESSURE TRANSMITTER)

Data is presented on the PC via the USB® fully configurable Windows Interface software. It has instant connection with auto-detection, and will configure automatically with your desktop, laptop or Windows tablet via USB protocol. The sample rate enables dynamic pressures to be measured with up to 21 bit resolution at user selectable speeds up to 1,000 Hz.

For real-time analysis, data transferred to the PC is achieved without loss of accuracy or bandwidth. Compatible with computers with 2.0/3.0x type A ports, the USB® interface configuration and analysis software runs on Windows 8, 8.1, 10 and 11. Data can be displayed in graphical or tabular form, with a choice of pressure units and fully adjustable scales and saved to a file or exported to Excel/PDF/CSV.

The USB® software has many features including custom certificate generation, customisable certificate templates, leak testing, record and view up to 16 sensors at the same time, virtual differential pressure measurement, set automatic test start and stop times, alarm levels for each individual sensor and excellent measurement accuracy which provides high resolution with a precision greater than 1 in 10,000. We are continually enhancing the USB software, and the auto-update feature means that you will never miss a new version.



The advanced sensor design consists of a piezoresistive silicon strain gauge circuit, which is epitaxially grown onto the surface of a sapphire diaphragm to form a single crystalline structure. The sapphire sensor element is then molecularly bonded to a titanium alloy sub-diaphragm.

This enables the sensor to endure higher overpressures and provides superb corrosion resistance. The sensor exhibits virtually no hysteresis and excellent long-term stability over wide temperature ranges.



TECHNICAL DATA

Type	AGD4200-USB	
Sensor Technology:	Silicon-on-Sapphire (SOS)	
Output Signal:	USB 2.0 compatible	
Supply Voltage:	5 Vdc via USB bus	
Pressure Reference:	Gauge (default); Absolute reference input by user	
Standard Pressure Ranges (bar):	-1 to 2.5 bar; 0-16 bar; 0-100 bar; 0-400 bar; 0-1000 bar; 0-1500 bar; 0-2000 bar; 0-3000 bar; 0-4000 bar; 0-5000 bar	
Standard Pressure Ranges (other):	User selectable for psi and other measurement units	
Overpressure Safety:	2x up to 400 bar; 1.5x for 1,000 bar; 1.1x for 1,500 bar; 1.5x for 2,000 bar; 1.25x for 3,000+ bar; 1.2x for 5,000 bar	
Accuracy NLHR:	Ranges to 3,000 bar: $\leq \pm 0.15\%$ of span BFSL	Ranges above 3,000 bar: $\leq \pm 0.35\%$ of span BFSL
Sample Rate:	User selectable to 1,000 samples per second (1,000 Hz) Resolution: 21 bits for ≤ 5 Hz; 16 bits for $> 5 - 1,000$ Hz	
Operating Ambient Temperature:	$-20\text{ }^{\circ}\text{C}$ to $+85\text{ }^{\circ}\text{C}$ ($-4\text{ }^{\circ}\text{F}$ to $+185\text{ }^{\circ}\text{F}$)	
Operating Media Temperature:	$-50\text{ }^{\circ}\text{C}$ to $+125\text{ }^{\circ}\text{C}$ ($-58\text{ }^{\circ}\text{F}$ to $+257\text{ }^{\circ}\text{F}$)	
Storage Temperature:	$+5\text{ }^{\circ}\text{C}$ to $+40\text{ }^{\circ}\text{C}$ ($+41\text{ }^{\circ}\text{F}$ to $+104\text{ }^{\circ}\text{F}$) Recommended Best Practice	
Temperature Effects:	$\pm 1.5\%$ FS total error band for $-10\text{ }^{\circ}\text{C}$ to $+80\text{ }^{\circ}\text{C}$. Typical thermal zero and span coefficients $\pm 0.015\%$ FS/ $^{\circ}\text{C}$	
Electromagnetic Compatibility:	EN61326-1, EN61326-2-3 (Laboratory equipment)	
Wetted Parts:	Titanium alloy	
Pressure Media:	All fluids compatible with titanium alloy	
Pressure Connection:	1/4" BSP male (G1/4); 1/4" NPT male or F250-C (Autoclave)	
Electrical Connection:	Standard version supplied with USB mini B to USB A 2m cable Heavy Duty version supplied with MIL-26482-1 8-4P to USB A 2m cable	
Software Compatibility:	Windows 8 8.1 10 11	
Net. Weight (Kg):	0.4 Kg	



ORDER MATRIX

Output	Type	Options	Pressure Range	Process Connection
Dynamic (1000 Hz)	AGD4200-USB			
Options				
USB Mini B		-		
MIL-26482-1 8-4P		B		
Pressure Range				
-1 to 2.5 bar			02.5	
0-16 bar			0016	
0-100 bar			0100	
0-400 bar			0400	
0-1000 bar			1000	
0-1500 bar			1500	
0-2000 bar			2000	
0-3000 bar			3000	
0-4000 bar			4000	
0-5000 bar			5000	
Process Connection				
1/4" BSP male (G1/4)				AB
1/4" NPT male				AM
Autoclave F-250-C female (for pressures above 1500 bar)				DE
Order Number Example		AGD4200-USB1500AB		

For options not listed please contact the sales team

DISCLAIMER: We reserve the right to change specifications without prior notice. specifications without prior notice. All manufactured products are calibrated with precision calibration equipment that is traceable to national measurement standards.